



BYNA590MRT15ACCC, Compression Terminal, 15 Degree, Accommodates Hamburg 570, Milan 590, Rome 610 ACCC



By Burndy
Catalog # [BYNA590MRT15ACCC](#)

HYLUG™ TERMINAL Without Hardware, CTC NO. 600-253-6,
Accommodates HAMBURG 570/MILAN 590/ROME 610 ACCC®
BURNDY, DIE 727,15 Degree, OVER-LAP CRIMPS.

Application

For ACCC Conductor, Corona free operation up to 230 KV

General

Catalog Number	BYNA590MRT15ACCC
Connector Type	Terminal
Die Index	727
Die Type	L727W
Feature - Barrel Style	Tapered
Installation Torque	300 in-lb
Recommended in-lb	
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810487716
UPC 12 Digit	7818104877166

Dimensions

Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	3.92 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	15.7 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.97 in

Dimension - Pad Width inch	3.22 in
Weight	2.8 lb

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACCC Str Size	HAMBURG 570 mm ² , MILAN 590 mm ² , ROME 610 mm ²
Conductor - Material	Aluminum

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50081944](#)
- [Specifications - BYNA590MRT15ACCC](#)