



FD65T14CG14, Substation - Copper Stud Connector

By Burndy
Catalog # [FD65T14CG14](#)

Stud Connector, 1.00 IN Stud to 4 Holes NEMA, Material: Cast Copper Alloy.



Application

Substation

General

Catalog Number	FD65T14CG14
Connector Type	Stud Connector
Installation Torque	360 lbs-in
Recommended in-lb	
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
Physical Attribute - Pad	In-line
Orientation	
Plated	Y
Plating Type	Tin Plated
Type	Studs
UPC	621945144392
UPC 12 Digit	6219451443922

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	2.68 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	167 mm
Dimension - Length Overall inch	6.56 in
Dimension - Pin Diameter fraction	1 in
Dimension - Pin Diameter inch	1.00 in
Dimension - Threads per inch	12
Dimension - Width inch	2.88 in

Conductor Related

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)