

FD66D6BRTN, Substation - Copper Stud Connector

By Burndy
Catalog # [FD66D6BRTN](#)



Copper Stud Connectors.

Application

Substation

General

Catalog Number	FD66D6BRTN
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin - Bright
Type	Studs
UPC	781810358153
UPC 12 Digit	7818103581533

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	4.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	174 mm
Dimension - Length Overall inch	6.84 in

Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	1-1/4 in
Dimension - Pin Diameter inch	1.250 in
Dimension - Thread Size	3/8-12
Dimension - Threads per inch	12

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD079583](#)
[Specifications - FD66D6BRTN](#)