




# CKSA6, Aluminum Split Bolt and Cover Kit

By Burndy  
Catalog # [CKSA6](#)

MAX RUN TO MAX TAP: #6 STR - #6 STR MIN RUN TO MIN TAP: #10 SOL - #10 SOL MAX RUN TO MIN TAP: #6 STR - #10 SOL TORQUE: 165 lb-in AL9CU.



## General

Installation Torque Recommended in-lb	165 LBS/in
Material	Aluminum
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	TRITAP™ SERVIT®
UPC	781810051627
UPC 12 Digit	7818100516277

## Dimensions

Dimension - Bolt Size inch	1.06 in
Dimension - Cross Flats inch	0.75 in
Dimension - Height fraction	2/3 in
Dimension - Height inch	0.64 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.28 in
Dimension - Width inch	0.56 in
Dimension - Width mm	14 mm

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - AL Str Run	8 AWG;6 AWG
Conductor - AL Str Run Range	8 AWG-6 AWG
Conductor - AL Str Tap	8 AWG;6 AWG
Conductor - AL Str Tap Range	8 AWG-6 AWG
Conductor - Copper Solid Run	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Run Range	10 AWG-6 AWG
Conductor - Copper Solid Tap	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Tap Range	10 AWG-6 AWG
Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Run Range	10 AWG-6 AWG
Conductor - Copper Str Tap	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Tap Range	10 AWG-6 AWG

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	7200

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-CKSA6-SPEC-EN | REV 1/2024