



CS3CI58220J, Medium Voltage Cold Shrink Termination Kit, 5-8kV 3-Phase Conversion Series-Indoor, Sleeve w/o Boot for Jacketed Concentric Conductor



By Burndy
Catalog # CS3CI58220J

The Type CS3CI58-J Series of 3 Phase Conversion Kits with Outdoor Sleeves without Boot for Jacketed Concentric Conductor. Conversion kits includes indoor cold shrinkable tube (unprinted), seal, cable tie, and installation guide. Conforms to IEEE-48-2009, Class 1 and ISO/IEC 17025 Standards. Test reports available upon request.

Features

- Rip and Grip does not require heat gun or any installation tools
- Spiral rip cord design provides for easy installation with effortless unwinding providing for fast removal of the hold-out core, Rip cord is recyclable
- All kits supplied with indoor cold shrinkable tube (unprinted), seal, cable tie, and installation guide
- Quick, easy, cost effective installation utilizing one-piece terminator design
- Test reports available upon request

Application

- To be used with Single Conductor, 5-8 kV XPLE and EPR non-shielded power cables for the Electrical/Industrial/Construction market.

General

Boot Type	NO
EU RoHS Indicator	Under Review
Environmental Conditions	Indoor
Material	Caoutchouc de silicone
Pin Type	N/A
Series	UD-JC
Terminal Type	N/A
Type	<ul style="list-style-type: none">• CS3CI58-J• CS3CI58-J
UPC	621945584990

Electrical Ratings

Phase	3-Phase
Voltage Rating	5/8 kV

Conductor Related

Conductor Range	<ul style="list-style-type: none">• 5-8kV: #2 AWG-250 kcmil• 15kV: #2-1 AWG
-----------------	--

Logistics

Carton Quantity	3
-----------------	---

Product Assets

[Brochures - Cold Shrink Medium Voltage Cable Terminations Brochure](#)
[Catalog Page - BURNDY_MVColdShrinkTerminationKits_CS3CI-J_CatCut](#)
[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50095782](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CS3CI58220J-SPEC-EN | REV 5/2024