



Medium Voltage Cold Shrink Kit

By Burndy

Catalog # [CSGO2528140](#)

Cold shrink cable terminations provide a quick, easy, safe and cost effective installation. No installation tools required, spiral rip cord design unwinds easily and enables quick removal of the hold-out core. Suitable for 25 to 28 kV Outdoor Industrial applications. Conforms to IEEE-48-1996, Class 1 and ISO/IEC 17025 Standards. Test reports available upon request.



Features

- Length of tube is consistent before and after application
- Rip and Grip does not require heat gun or any installation tools
- Spiral rip cord design provides for easy installation with effortless unwinding providing for fast removal of the hold-out core, Rip cord is recyclable
- All kits supplied with cold shrink termination sub assembly, center end seal termination, external grounding kit, braid (without sealant), violet PVC tape, and installation guide
- Variations supplied with terminal or pin connector require customer to crimp onto conductor during installation and would require proper installation tooling
- Insulating tube offers weathering and track resistance
- Test reports available upon request

Application

To be used with Single Conductor, 25 - 28 kV XLPE and EPR copper tape, drain wire, single shield or lead sheathed power cables for the Electrical/Industrial/Construction market

General

Boot Type	NO
Environmental Conditions	Outdoor
Material	Caoutchouc de silicone
Series	G
Type	CSGO2528
UPC	621945584495

Electrical Ratings

Phase	1-Phase
Voltage Rating	25/28 kV

Conductor Related

Conductor Range	#1 - 4/0 AWG
-----------------	--------------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Brochures - Cold Shrink Medium Voltage Cable Terminations Brochure](#)
[Catalog Page - BURNDY_MVColdShrinkTerminationKits_CSGO_CatCut](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50095762](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-CSGO2528140-SPEC-EN | REV 5/2023