


# FD67D8T14, Substation - Copper Stud Connector

By Burndy  
Catalog # [FD67D8T14](#)



## Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

## Application

Substation

## General

Catalog Number	FD67D8T14
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810077740
UPC 12 Digit	7818100777400

## Dimensions

Dimension - B Length inch	2.18 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.00 in
Dimension - F Width Center to Center inch	1.75 in

Dimension - Height mm	0 mm
Dimension - L Length Overall mm	185 mm
Dimension - Length Overall inch	7.30 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	1-1/2 in
Dimension - Pin Diameter inch	1.500 in
Dimension - Thread Size	1/2-14
Dimension - Threads per inch	14

## Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	2
-----------------------	---

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - FD67D8T14](#)