



# FD67T12CG14, Substation - Copper Stud Connector

By Burndy  
Catalog # [FD67T12CG14](#)

Stud Connector, 1-1/2 IN Stud to 4 Holes NEMA Pad, Material: Cast Copper Alloy.



## Application

Substation

## General

Connector Type	Stud Connector
Installation Torque Recommended in-lb	360 lbs-in
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin Plated
Type	Studs
UPC	621945144484
UPC 12 Digit	6219451444844

## Dimensions

Dimension - B Length inch	2.68 in
Dimension - Length Overall inch	6.56 in
Dimension - Pin Diameter inch	1.50 in
Dimension - Threads per inch	12
Dimension - Width inch	2.88 in

## Conductor Related

Conductor - Connection Combination Stud to Bar

## Certifications And Compliance

Certification - CSA Approved No  
Standards - RoHS Compliance UI Status

## Logistics

Minimum Pack Quantity 1

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-FD67T12CG14-SPEC-EN | REV 5/2024