



CTNT50200D0, Cable Tie, 2" Max Bundle, 50 Lb Tensile, Black, Nylon 12

By Burndy
Catalog # [CTNT50200D0](#)

Nylon 12 Cable Tie, Tensile strength: 50 Lbs, Color: Black, 7.50"L, 0.19"W, 2.00" Bundle Dia.



Features

- Nylon 12 Cable Ties provide excellent UV, chemical and moisture resistant
- Ties feature inside serrations and bent tail for quick, easy installation
- Smooth edge to prevent bundle damage
- Especially suitable in high moisture, corrosive (zinc chloride and dilute acids) environments
- Good in low temperatures
- Indoor/Outdoor applications

General

| | |
|---------------------------------------|----------------|
| Catalog Number | CTNT50200D0 |
| Color | Black |
| Material | NYLON 12 |
| Rating - Minimum Tensile Strength lbs | 50 lb |
| Tensile Strength | 50 / 22 lb./Kg |
| Trade Name | UNIRAP™ |
| UPC | 621945469426 |

Dimensions

| | |
|-----------------------------|---------|
| Dimension - Bundle Diameter | 2.00 in |
| Max inch | |

| | |
|------------------------------|---------|
| Dimension - L Length Overall | 190 mm |
| mm | |
| Dimension - Length Overall | 7.50 in |
| inch | |
| Dimension - Width inch | 0.19 in |
| Dimension - Width mm | 4.8 mm |
| Thickness | 0.05 in |

Certifications And Compliance

| | |
|------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance | CM |
| Status | |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 15000 |
| Minimum Pack Quantity | 500 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50071686](#)
- [Sell Sheets - Nylon 12 Cable Tie Group](#)
- [Specifications - CTNT50200D0](#)