

## CUW44E, Copper Alloy Deadend Strain Clamp, 500-1000 kcmil

By Burndy  
Catalog # CUW44E



Cast Cu Alloy Deadend Strain clamp, 500 - 1000 Kcmil Cu, Bright Dipped.

### Features

- High strength, two-bolt
- Single saddle design for short span distribution and strain bus application
- Galvanized steel clevis pin and U-bolts

### General

Catalog Number	CUW44E
Connector Type	Deadend
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Bright Dipped
UPC	781810091753

### Dimensions

Dimension - B Length fraction	3-1/4 in
Dimension - B Length inch	3.25 in
Dimension - Height fraction	3-3/8 in
Dimension - Height inch	3.3 in
Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in
Dimension - Width fraction	4-44/83 in
Dimension - Width inch	4.53 in
Dimension - Width mm	115 mm

### Conductor Related

Conductor - Copper Str Size	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	500 kcmil-1000 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Product Cross Section Image\(s\) - BUR\\_CUW\\_LineArt](#)
- [Sales Drawings - sd046598-01](#)
- [Specifications - CUW44E](#)