




# FD70F16W, Substation - Copper Stud Connector

By Burndy

Catalog # [FD70F16W](#)



Copper Stud Connectors.

## Application

Substation

## General

Catalog Number	FD70F16W
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	6
Physical Attribute - Pad Configuration	6x4 - 6 holes
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin - Hot Dipped
Type	Studs
UPC	781810252314
UPC 12 Digit	7818102523144

## Dimensions

Dimension - B Length inch	2.88 in
Dimension - Bolt Size fraction	5/8
Dimension - D inch	4.00 in
Dimension - L Length Overall mm	233 mm
Dimension - Length Overall inch	9.19 in
Dimension - N inch	1.13 in
Dimension - Pad Width inch	6.00 in

Dimension - Pin Diameter fraction	3 in
Dimension - Pin Diameter inch	3.000 in
Dimension - Thread Size	5/8-12
Dimension - Threads per inch	12

## Electrical Ratings

Amperage Rating	4000 A
-----------------	--------

## Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - SD079583](#)

[Specifications - FD70F16W](#)