

CY4/OL17G5TN Rope Lay Braid

By Burndy

Catalog # [CY4/OL17G5TN](#)



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	CY4/OL17G5TN
Connector Type	Braid
Material	Copper
UPC	781810665336
UPC 12 Digit	7818106653366

Dimensions

Dimension - L Length Overall mm	432 mm
Dimension - Length Overall inch	17 in

Length	17 in
Weight	0.235 lb

Electrical Ratings

Amperage Rating	335 A
-----------------	-------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	40
Pallet Quantity	1920

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50038434](#)
- [Specifications - BURNDY_CY40L17G5TN_Specsheet](#)
- [Specifications - CY4/OL17G5TN](#)