



# FD72D16T10TN, Substation - Copper Stud Connector

By Burndy  
Catalog # [FD72D16T10TN](#)

Copper Stud Connectors.



## Application

Substation

## General

Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin - Electro Plated
Type	Studs
UPC	781810256695
UPC 12 Digit	7818102566955

## Dimensions

Dimension - B Length inch	3.00 in
Dimension - Bolt Size fraction	5/8
Dimension - D inch	4.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	214 mm
Dimension - Length Overall inch	8.42 in
Dimension - N inch	1.13 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	4 in
Dimension - Pin Diameter inch	4.000 in
Dimension - Thread Size	5/8-10
Dimension - Threads per inch	10

## Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-FD72D16T10TN-SPEC-EN | REV 8/2023