



EP Series Electric/Hydraulic Pump, 10000 psi, 17-1/2" high

By Burndy
Catalog # [EP10](#)

Pump, EP10 Series, 10K psi.



Features

- 1/2 HP motor
- Dual voltage/hertz
- Roll cage
- Quick disconnect hydraulic coupler
- Oil level window
- 8 quart reservoir
- Factory set output pressure

Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
EU RoHS Indicator	Yes
Power Source	1/2 HP 115/230V-AC; 60 Cycle; 1/2 HP @ 3450 RPM
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810033401
UPC 12 Digit	7818100334011

Dimensions

Dimensions	18.50 in x 11.75 in x 17.50 in
Height	17.5 in
Length	18.5 in
Weight	68 lb
Width	11.75 in

Electrical Ratings

Current Draw Max	10 Amperes
------------------	------------

Certifications And Compliance

Standards - RoHS Compliance CM
Status

Logistics

Minimum Pack Quantity	1
Package Contents	Pump only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_082_OWMF_EP10_lineart](#)
[Sales Drawings - SE..207894B](#)
[SDS - ALFLUID SDS \(GHS\) \(2021-07\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-EP10-SPEC-EN | REV 5/2024