

# FDA70D12, Substation - Copper Stud Connector

By Burndy  
Catalog # FDA70D12



Copper Stud Connectors.

## Application

Substation

## General

Catalog Number	FDA70D12
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Pad Orientation	90 Degree - horizontal
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810196489
UPC 12 Digit	7818101964899

## Dimensions

Dimension - B Length inch	2.88 in
Dimension - D inch	4.00 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	233 mm
Dimension - Length Overall inch	9.19 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in

Dimension - Pin Diameter fraction	3 in
Dimension - Pin Diameter inch	3 in
Dimension - Threads per inch	12

## Electrical Ratings

Amperage Rating	2100 A
-----------------	--------

## Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd079588-01](#)
- [Specifications - FDA70D12](#)