



EP10 Pump with Foot Control, 10,000 psi

By Burndy
Catalog # [EP10FC](#)

Pump, EP10 Series, 10K psi, Foot Control.



Features

Foot Control

Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	EP10FC
Power Source	1/2 HP 115/230V-AC; 60 Cycle; 1/2 HP @ 3450 RPM
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810036556
UPC 12 Digit	7818100365566

Dimensions

Dimensions	18.50 in x 11.75 in x 17.5 in
Height	17.5 in
Length	18.5 in
Weight	68 lb
Width	11.75 in

Electrical Ratings

Current Draw Max 10 Amperes

Certifications And Compliance

Standards - RoHS Compliance CM
Status

Logistics

Minimum Pack Quantity 1
Package Contents Pump, Foot Control

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_EP10_LineArt](#)
[SDS - ALFLUID SDS](#)
[Specifications - EP10FC](#)