



# FD64C5, Substation - Copper Stud Connector

By Burndy  
Catalog # [FD64C5](#)

Copper Stud Connector to 4 Hole NEMA Pad.



## Application

Substation

## General

Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	3x3 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810077566
UPC 12 Digit	7818100775666

## Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.82 in
Dimension - Pad Width inch	3.00 in
Dimension - Pin Diameter fraction	3/4 in
Dimension - Pin Diameter inch	0.750 in
Dimension - Thread Size	3/8-12
Dimension - Threads per inch	12
Dimension - Width mm	76.2 mm

## Conductor Related

Conductor - Connection Combination Stud to Pad

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity 4

## Product Assets

[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-FD64C5-SPEC-EN | REV 8/2023

