



FD655D6, Substation - Copper Stud Connector, 4-Holes, 1/2" Stud, 1.75" Spacing, Stud to Flat Bar

By Burndy
Catalog # [FD655D6](#)

Cast Cu Alloy Stud Connector, 1300 Amps Indoor Nom, 0.56" Hole Size, 1.75" Spacing, Bolted, Stud to Flat Bar, 1-1/8"- 12 Stud Dia, 4 NEMA Pad Holes.



Application

Substation

General

Connector Type	Stud Connector
EU RoHS Indicator	Yes
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Pad Configuration	4x4 - 4 holes
Plated	N
Plating Type	Unplated
Sub Brand	STUD CONNECTOR
Type	Studs
UPC	781810003602
UPC 12 Digit	7818100036022

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	4.00 in
Dimension - L Length Overall mm	174 mm
Dimension - Length Overall inch	6.86 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	1-1/8 in
Dimension - Pin Diameter inch	1.125 in
Dimension - Thread Size	3/8-12
Dimension - Threads per inch	12

Electrical Ratings

Amperage Rating 1300 A

Conductor Related

Conductor - Connection Combination Stud to Pad

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - FD655D6_MODEL-PDF](#)
[3D Models - FD655D6_MODEL-IGES](#)
[3D Models - FD655D6_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD079583](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-FD655D6-SPEC-EN | REV 8/2023