




GAR3904TC, Mechanical Ground Connector, For 2 Hole Lug to Pipe or Rod

By Burndy
Catalog # [GAR3904TC](#)

Water Pipe Ground Connector, 2-1/2"- 3-1/2" Rod, Large, smooth connector contact area between pipe and ground clamp



Features

- Large, smooth connector contact area between pipe and ground clamp to maximize contact area between connector and pipe
- Pre-drilled pad for 2-3/8" bolts on 1" centers to allow for direct mounting of 2-hole compression terminals up to 750 kcmil to pipe
- One-wrench installation
- UL467 Listed for the US and Canadian Markets

General

| | |
|--|--|
| Application | For Direct Burial, Water Pipe As Well As Structural And Reinforcing Rod Shapes |
| Catalog Number | GAR3904TC |
| EU RoHS Indicator | Yes |
| Installation Torque | 240 LBS/in |
| Recommended in-lb | |
| Material | Copper Alloy |
| Material - Hardware | DURIUM™ Silicon Bronze |
| Physical Attribute - Number of Holes | 3 |
| Physical Attribute - Pad Configuration | 2.50 x 2.50 - 3 Holes |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | MECHANICAL CONNECTOR |
| Type | Rod or Tube Clamp with Mounting Pad |
| U Bolt Type | 1033 |
| UPC | 781810001578 |
| UPC 12 Digit | 7818100015788 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Height inch | 6.50 in |
| Dimension - Length Overall inch | 2.50 in |
| Dimension - Outside Diameter inch | 4.00 in |
| Dimension - Thread Size | 3/8-16 |
| Dimension - Threads per inch | 16 |
| Dimension - Width inch | 6.50 in |
| Dimension - Width mm | 165 mm |

Conductor Related

| | |
|---------------------------------------|--------------|
| Conductor - Copper Tube EH Size | 2 1/2;3 1/2 |
| Conductor - Copper Tube EH Size Range | 2 1/2-3 1/2 |
| Conductor - Pipe or Round Tube Size | 2.5 - 3.5 in |

Certifications And Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical](#)

[Grounding](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_GAR3900_Lineart](#)

[Sales Drawings - se..206158-01](#)

