



FD655D6U, Substation - Copper Stud Connector, 4-Hole Pad, 1-1/8" Stud to NEMA Pad

By Burndy
Catalog # [FD655D6U](#)

Copper Stud Connector, 1-1/8 IN Stud to 4 Hole NEMA Pad, 6.86 IN L.



Application

Substation

General

Catalog Number	FD655D6U
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Pad Configuration	4x4 - undrilled
Physical Attribute - Pad Orientation	In-line
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810221891
UPC 12 Digit	7818102218911

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	4.25 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	174 mm
Dimension - Length Overall inch	6.86 in
Dimension - N inch	1.13 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	1-1/8 in
Dimension - Pin Diameter inch	1.125 in
Dimension - Thread Size	3/8-12
Dimension - Threads per inch	12
Dimension - Width mm	101.6 mm

Conductor Related

Conductor - Connection Combination Stud to Pad

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog Interactive Catalog - BURNDY Full-Line Digital Catalog](#)



A Hubbell brand