



FD65TOCG2, Substation - Copper Stud Connector

By Burndy
Catalog # [FD65TOCG2](#)

Stud Connector, 1.00 IN Smooth Stud to 4 Holes NEMA,
Material: Cast Copper Alloy.



Application

Substation

General

Connector Type	Stud Connector
Installation Torque Recommended in-lb	360 lbs-in
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin Plated
Type	Studs
UPC	621945144385
UPC 12 Digit	6219451443855

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	2.68 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	167 mm
Dimension - Length Overall inch	6.56 in
Dimension - Pin Diameter fraction	1 in
Dimension - Pin Diameter inch	1.00 in
Dimension - Width inch	2.88 in

Conductor Related

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-FD65TOCG2-SPEC-EN | REV 8/2023