




GB29, Mechanical Grounding Connector, Cable to Bar

By Burndy
Catalog # [GB29](#)

Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 2/0 AWG (Sol) -250 kcmil, 1/2" Stud, 2 IN Width.



Application

For Copper Cable To Bar, Direct Burial Cable

General

EU RoHS Indicator	Yes
Installation Torque	480 lb-in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GB
UPC	781810231272
UPC 12 Digit	7818102312722

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Height inch	2.32 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.88 in

Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - GB29_MODEL-IGES](#)
[3D Models - GB29_MODEL-PDF](#)
[3D Models - GB29_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_GB_Lineart](#)
[Sales Drawings - sc091657-01](#)



A proud member of the Hubbell Family.