




FD675D12M40TOHQ, Substation - Copper Stud Connector

By Burndy

Catalog # [FD675D12M40TOHQ](#)



Stud Terminal, M40, Material: Cast Copper Alloy.

Application

Substation

General

Catalog Number	FD675D12M40TOHQ
Connector Type	Stud Terminal
Installation Torque	480 lbs-in
Recommended in-lb	
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810446447
UPC 12 Digit	7818104464477

Dimensions

Dimension - B Length inch	2.18 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	200 mm

Dimension - Length Overall inch	7.88 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	1-3/4 in
Dimension - Pin Diameter inch	1.750 in
Dimension - Width inch	4.00 in

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - FD675D12M40TOHQ](#)