

FD67CG39, Substation - Copper Stud Connector

By Burndy
Catalog # [FD67CG39](#)



Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

General

Catalog Number	FD67CG39
Connector Type	Stud Connector
Installation Torque	360 lbs-in
Recommended in-lb	
Material	Copper Alloy, Cast
Material - Hardware	Durium
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	3.5x3.75 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810450444
UPC 12 Digit	7818104504444

Dimensions

Dimension - B Length inch	2.62 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.75 in

Dimension - F Width Center to Center inch	1.75 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	187 mm
Dimension - Length Overall inch	7.38 in
Dimension - N inch	0.88 in
Dimension - Pad Width inch	3.50 in
Dimension - Pin Diameter inch	1.50 in
Dimension - Threads per inch	12
Dimension - Width inch	3.50 in

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - CSC032410-01](#)
- [Specifications - FD67CG39](#)