



GBL30GS, Mechanical Grounding Connector, Cable to Bar, Galvanized Steel

By Burndy
Catalog # [GBL30GS](#)



Cast Copper Alloy Ground Connector, 4 AWG (SOL) - 300 KCMIL, 1/2" Stud, 1 1/2" Width Galvanized Steel Hardware.

General

Installation Torque Recommended in-lb	480 lb-in
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810100912
UPC 12 Digit	7818101009122

Dimensions

Dimension - Bus Thickness inch	0.32 in
Dimension - Height inch	2.32 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.88 in
Dimension - Stud Size inch	33/64
Dimension - Width inch	1.50 in
Dimension - Width mm	38 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	4 AWG - 300 KCMIL
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
Conductor - Copper Str Size Range	4 AWG - 300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	24
-----------------------	----

Product Assets

[3D Models - GBL30GS_MODEL-STEP](#)
[3D Models - GBL30GS_MODEL-PDF](#)
[3D Models - GBL30GS_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sa209089-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GBL30GS-SPEC-EN | REV 1/2024