



GCS26TN, Ground Clamp to Steel Connector, Tin Plated

By Burndy
Catalog # [GCS26TN](#)

Ground clamp to steel connector, Conductor range from #6 AWG to 2/0 AWG, Tin plated.



Features

- cULus for Grounding and Bonding, Direct Burial rated for installation into earth and concrete
- Accepts beam thickness: .125 - .625" (1/8 to 5/8")
- Conductor range from #6 to 2/0
- Versatile, allows parallel or perpendicular conductor orientation
- Stainless steel hardware
- 5/32" Allen cup point screw penetrates coatings on steel
- No special tooling required
- Applicable for use in "extremely volatile environments"

Application

Applicable for use in extremely volatile environments

General

EU RoHS Indicator	Contact Manufacturer
Installation Torque Recommended in-lb	180 in-lb on hex nut; 100 in-lb on Allen screw
Material	Copper Alloy, Cast
Material - Hardware	Stainless Steel
Plated	Yes
Plating Type	Tin Plated
Sub Brand	THE CONSTRICTOR
Type	GCS
UPC	621945516151

Dimensions

Dimensions	3.00 in x 1.60 in x 2.70 in
Height	2.7 in
Length	3 in
Width	1.6 in

Conductor Related

Conductor - Copper Str Size	#6 to 2/0
-----------------------------	-----------

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50089428](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GCS26TN-SPEC-EN | REV 5/2024