



# FD67T12144NTN, Substation - Copper Stud Connector

By Burndy  
Catalog # [FD67T12144NTN](#)

Copper Stud Connectors.



## Application

Substation

## General

Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x3 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin - Electro Plated
Type	Studs
UPC	621945105324
UPC 12 Digit	6219451053244

## Dimensions

Dimension - B Length inch	2.69 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	165 mm
Dimension - Length Overall inch	6.50 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter inch	1.500 in
Dimension - Thread Size	1/2-12
Dimension - Threads per inch	12

## Conductor Related

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-FD67T12144NTN-SPEC-EN | REV 8/2023