



FD685D16SV, Substation - Copper Stud Connector

By Burndy
Catalog # [FD685D16SV](#)

Copper Stud Connectors.



Application

Substation

General

Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Silver
Type	Studs
UPC	781810438329
UPC 12 Digit	7818104383299

Dimensions

Dimension - B Length inch	2.50 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.77 in
Dimension - N inch	1.13 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	2-1/4 in
Dimension - Pin Diameter inch	2.250 in
Dimension - Thread Size	1/2-12
Dimension - Threads per inch	12

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications and Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD079583](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-FD685D16SV-SPEC-EN | REV 8/2023