

GD1729, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy
Catalog # GD1729



Mechanical Grounding Connector, 2 Cables to Rod or Tube, 2/0 AWG (Sol) -250 kcmil, 1-1/2" Pipe, 1-5/8"-1-7/8" Rod.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

General

| | |
|-----------------------|------------------------|
| Catalog Number | GD1729 |
| EU RoHS Indicator | Yes |
| Installation Torque | 240 LBS/in |
| Recommended in-lb | |
| Material | Copper Alloy, Cast |
| Material Type - Screw | DURIUM™ Silicon Bronze |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | MECHANICAL CONNECTOR |
| Type | GD |
| U Bolt Type | 268 |
| UPC | 781810260302 |
| UPC 12 Digit | 7818102603022 |

Dimensions

| | |
|-----------------------------|----------|
| Dimension - B Length inch | 1.31 in |
| Dimension - Height fraction | 4 in |
| Dimension - Height inch | 4.00 in |
| Dimension - Width fraction | 3-1/4 in |
| Dimension - Width inch | 3.25 in |
| Dimension - Width mm | 83 mm |

Conductor Related

| | |
|--|----------------------------|
| Conductor - Copper Solid Size | 2/0;3/0;4/0 |
| Conductor - Copper Solid Size Range | 2/0-4/0 |
| Conductor - Copper Str Size | 2/0;3/0;4/0;250 |
| Conductor - Copper Str Size B Range | 1.5 |
| Conductor - Copper Str Size Range | 2/0 AWG - 250 kcmil |
| Conductor - Copper Tube Std Size | 1-5/8;1-3/4;1-7/8 |
| Conductor - Copper Tube Std Size Range | 1-5/8-1-7/8 |
| Conductor - Rod Size | 1 5/8 in;1 3/4 in;1 7/8 in |
| Conductor - Rod Size Range | 1 5/8 in-1 7/8 in |

Certifications And Compliance

| | |
|---|-------|
| Buy American Compliant | Yes |
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[3D Models - GD1729_MODEL-IGES](#)

[3D Models - GD1729_MODEL-PDF](#)

[3D Models - GD1729_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical](#)

[Grounding](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_gdla](#)

[Sales Drawings - SD..013775-01](#)

[Specifications - GD1729](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-GD1729-SPEC-EN | REV 8/2024