



FD68G149TN, Substation - Copper Stud Connector

By Burndy
Catalog # [FD68G149TN](#)

Copper Stud Connectors.



Application

Substation

General

Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x7.75 - 8 holes
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin - Electro Plated
Type	Studs
UPC	781810118689
UPC 12 Digit	7818101186899

Dimensions

Dimension - B Length inch	2.03 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	7.75 in
Dimension - L Length Overall mm	283 mm
Dimension - Length Overall inch	11.16 in
Dimension - N inch	1.25 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	2 in
Dimension - Pin Diameter inch	2.000 in
Dimension - Thread Size	1/2-12
Dimension - Threads per inch	12

Conductor Related

Conductor - Connection Combination Stud to Pad

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity 1

Product Assets

[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-FD68G149TN-SPEC-EN | REV 8/2023