



## GD1929, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy  
Catalog # GD1929

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 2-1/2" to 2-7/8" Rod, 2-1/2" Pipe.



### Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

### Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

### General

Catalog Number	GD1929
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GD
U Bolt Type	266
UPC	781810238950
UPC 12 Digit	7818102389500

### Dimensions

Dimension - B Length inch	1.38 in
Dimension - Height fraction	5 in
Dimension - Height inch	5.00 in
Dimension - Width fraction	4-1/4 in
Dimension - Width inch	4.19 in
Dimension - Width mm	106 mm

### Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	2.5
Conductor - Copper Str Size	2/0 AWG - 250 kcmil
Conductor - Copper Str Size Range	
Conductor - Copper Tube Std Size	2-1/2
Conductor - Copper Tube Std Size Range	2-1/2
Conductor - Rod Size	2 1/2 in
Conductor - Rod Size Range	2 1/2 in

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[3D Models - GD1929\\_MODEL-PDF](#)

[3D Models - GD1929\\_MODEL-IGES](#)

[3D Models - GD1929\\_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical](#)

[Grounding](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR\\_gdla](#)

[Sales Drawings - SD..013775-01](#)

[Specifications - GD1929](#)

[Specifications - BURNDY\\_GD1929\\_Specsheet](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY-GD1929-SPEC-EN | REV 8/2024