



FD68T12CG9, Substation - Copper Stud Connector

By Burndy
Catalog # [FD68T12CG9](#)

Stud Connector, 2 IN Stud to 4 Holes NEMA Pad, Material: Cast Copper Alloy.



Application

Substation

General

Connector Type	Stud Connector
Installation Torque Recommended in-lb	360 lbs-in
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin Plated
Type	Studs
UPC	621945144569
UPC 12 Digit	6219451445699

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Length Overall inch	6.56 in
Dimension - Pin Diameter fraction	2 in
Dimension - Pin Diameter inch	2.00 in
Dimension - Threads per inch	12
Dimension - Width inch	2.88 in

Conductor Related

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-FD68T12CG9-SPEC-EN | REV 8/2023