

# GD1934, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy  
Catalog # [GD1934](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 300 - 500 kcmil, 2-1/2" Rod, 2-1/2" Pipe.

## Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

## General

Catalog Number	GD1934
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
U Bolt Type	232
UPC	781810260371
UPC 12 Digit	7818102603711

## Dimensions

Dimension - B Length inch	1.56 in
Dimension - Height fraction	5 in
Dimension - Height inch	5.00 in
Dimension - Width fraction	4-5/8 in
Dimension - Width inch	4.56 in
Dimension - Width mm	116 mm

## Conductor Related

Conductor - Copper Str Size	300;350;400;450;500
Conductor - Copper Str Size B Range	2.5
Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Copper Tube Std Size	2.5
Conductor - Copper Tube Std Size Range	2.5
Conductor - Rod Size	2 1/2 in
Conductor - Rod Size Range	2 1/2 in

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	864

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_gdla](#)
- [Sales Drawings - SD..013775-01](#)
- [Specifications - GD1934](#)



A Hubbell brand