


FD69D12, Substation - Copper Stud Connector

By Burndy
Catalog # [FD69D12](#)



Copper Stud Connectors.

Application

Substation

General

Catalog Number	FD69D12
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Pad Configuration	4x4 - 4 holes
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810077658
UPC 12 Digit	7818100776588

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.00 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	204 mm
Dimension - Length Overall inch	8.03 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	2-1/2 in
Dimension - Pin Diameter inch	2.500 in

Dimension - Thread Size	1/2-12
Dimension - Threads per inch	12

Electrical Ratings

Amperage Rating	2100 A
-----------------	--------

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD079583](#)
- [Specifications - FD69D12](#)