

GD2226, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy
Catalog # GD2226

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 4" to 4-1/2" Rod, 4" Pipe.



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

General

Catalog Number	GD2226
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GD
U Bolt Type	261
UPC	781810260463
UPC 12 Digit	7818102604633

Dimensions

Dimension - B Length inch	1.63 in
Dimension - Height fraction	6-3/8 in
Dimension - Height inch	6.38 in
Dimension - Width fraction	5-7/8 in
Dimension - Width inch	5.81 in
Dimension - Width mm	148 mm

Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size	4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	4
Conductor - Copper Str Size	4 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	4
Conductor - Copper Tube Std Size Range	4
Conductor Size	#4 Sol AWG - 2/0 Str AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_gdla](#)
[Sales Drawings - SD..013775-01](#)
[Specifications - BURNDY_GD2226_Specsheet](#)
[Specifications - GD2226](#)



A Hubbell brand