



GIB5, Intersystem Bonding Connector

By Burndy
Catalog # [GIB5](#)



The GIB5 Intersystem Bonding Connector meets the NEC Article 250.94 “Bonding for Other Systems” requirement. The NEC requirement dictates that all telephone, cable, and satellite grounding conductors must be tied together at one location to the grounding electrode conductor (GEC) in residential and commercial applications.

Features

- GIB5 is installed via a #8-#14 screw adjacent to the meter base or service entrance equipment
- The GIB5 accepts a main ground conductor from #2 to #6 AWG and up to four intersystem conductors from #4 to #14
- The GIB5 contains corrosion-resistant stainless steel wire binding screws, zinc connector body, and a white UV-stabilized cover
- UL467 Listed for the US and Canadian Markets

General

Catalog Number	GIB5
Material	Body: Zinc Alloy; Screw: Stainless Steel; Cover: White UV Stabilized Polycarbonate
Type	Intersystem Bonding
UPC	621945666870

Dimensions

Dimensions	3.39 in x 1.5 in x 1 in
------------	-------------------------

Height	1 in
Length	3.39 in
Width	1.5 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes

Logistics

Carton Quantity	54
-----------------	----

Product Assets

- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sell Sheets - BONDIT® Wall Mounted Intersystem Bonding Connectors](#)
- [Specifications - GIB5](#)