

FDA68G28, Substation - Copper Stud Connector

By Burndy
Catalog # [FDA68G28](#)



Copper Stud Connectors.

Application

Substation

General

Catalog Number	FDA68G28
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Pad Orientation	90 Degree - horizontal
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810368657
UPC 12 Digit	7818103686577

Dimensions

Dimension - D inch	3.94 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	243 mm
Dimension - Length Overall inch	9.57 in
Dimension - N inch	0.98 in

Dimension - Pad Width inch	3.94 in
Dimension - Pin Diameter fraction	2 in
Dimension - Pin Diameter inch	2 in
Dimension - Threads per inch	11

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - FDA68G28](#)