



Manual Hydraulic Foot Pump, 6000 psi, 1-1/8 Quarts Reservoir Volume

By Burndy
Catalog # [FP6](#)



Pump, Foot, 6K psi, 1-1/8 Quarts.

Features

- Diamond plate steel foot pad
- Long arm
- Spring loaded arm
- Built-in factory set pressure relief valve
- Quick disconnect hydraulic fitting
- Lightweight rugged design - portable
- Sturdy leg stabilizers

Application

Pumping

General

Application - For Use On	Use with 6,000 psi Y29BH Remote Hydraulic Crimper
Catalog Number	FP6
Tool Type	Pump, Manual Hydraulic
Type	Pump
UPC	781810008348
UPC 12 Digit	7818100083488

Dimensions

Length	24.75 in
Weight	19 lb
Width	5 in

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Pump only

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_FP10_LA](#)
- [Sales Drawings - SE207590](#)
- [Specifications - FP6](#)