



# GSC632N25B5H, Temporary Protective Ground Stud, Tin Plated Cast Copper, Inline NEMA Pad, 25 mm ball stud, Grade 5H

By Burndy  
Catalog # [GSC632N25B5H](#)

Temporary Protective Ground Studs are single point ground connections for Temporary Ground Sets. The Burndy H-Rated Ground Studs are designed and tested to meet the requirements of ASTM F855 Table 2.

## Features

- ASTM F855 Grade 5H Tested and Rated
- Third-party laboratory test results available
- 25mm Ball Stud
- Inline pad
- NEMA spacing for 1/2" Hardware
- Cast copper alloy
- Tin-plated for corrosion resistance
- Stud Cover Available - GSC632NH1BCOVER1

## General

Catalog Number	GSC632N25B5H
Material	Tin-Plated Copper Alloy
Type	Temporary Protective Ground Stud
UPC	621945689077

## Dimensions

Dimensions	7.87 in x 1.25 in x 1.5 in
------------	----------------------------



Height	1.5 in
Length	7.87 in
Width	1.25 in

## Certifications And Compliance

Buy America(n) Qualified      Contact Manufacturer

## Product Assets

- [3D Models - GSC632N25B5H STP](#)
- [Catalog Page - BURNDY Master Catalog Page E-75](#)
- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - GSC632N25B5H Drawing](#)
- [Sell Sheets - Temporary Protective Ground Studs](#)
- [Specifications - GSC632N25B5H](#)
- [Video - Temporary Protective Ground Studs](#)