



GSTUD916HY Structural Steel Ground Stud

By Burndy
Catalog # [GSTUD916HY](#)

Structural Steel Grounding Connector; Accommodates: 1/0 AWG, 5/8" Rod.



Features

- May be welded to steel surfaces quickly and easily
- No disk grinding needed
- Knurled surface for better gripping
- Copper plated
- May be installed during adverse weather conditions

Application

For Compression Connectors And Mechanical Connectors

General

EU RoHS Indicator	Yes
Material	Steel
Plated	Y
Plating Type	Nickel
Sub Brand	HYGROUND, VERSITAIL
Trade Name	VERSITAIL™
Type	<ul style="list-style-type: none">• GSTUD-HY• GSTUD-HY
UPC	781810220894
UPC 12 Digit	7818102208944

Dimensions

Dimension - B Length fraction	53/93 in
Dimension - B Length inch	0.57 in
Dimension - D inch	1.25 in
Dimension - Ground Rod Size	5/8 in
Dimension - L Length Overall mm	144 mm
Dimension - Length Overall inch	5.68 in
Physical Attribute - Tongue Angle	45 Degree

Conductor Related

Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Rod Size	5/8 in
Conductor - Rod Size Range	5/8 in
Conductor Type	<ul style="list-style-type: none">• Rod-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	3920

Product Assets

[3D Models - GSTUD916HY_MODEL-IGES](#)
[3D Models - GSTUD916HY_MODEL-PDF](#)
[3D Models - GSTUD916HY_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd..086414-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GSTUD916HY-SPEC-EN | REV 1/2024

