



**HSB14FR, Heat Shrink Tubing,
0.250" ID Min.(Exp.), 0.125" ID Max.
(Rec.), 12-10 Flex, PVC, Thin Wall,
Flame Retardant, Black, 600V.**



By Burndy
Catalog # [HSB14FR](#)

Heat Shrink Tubing, 0.250" ID Min.(Exp.), 0.125" ID Max.(Rec.), 12-10 Flex, PVC, Thin Wall, Flame Retardant, Black, 600V.

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

General

| | |
|-------------------|--|
| Catalog Number | HSB14FR |
| Connector Type | THIN WALL TUBES/REELS |
| EU RoHS Indicator | Yes |
| Material | Polyvinyl chloride |
| Sub Brand | HEAT SHRINK |
| Type | HS-FR, Thin Wall, Flexible, Fire Retardant |
| UPC | 781810265819 |

Conductor Related

| | |
|-----------------|--------------------|
| Conductor Range | #12 AWG to #10 AWG |
|-----------------|--------------------|

| | |
|----------------|-------------|
| Conductor Size | 12AWG -8AWG |
|----------------|-------------|

Certifications And Compliance

| | |
|------------------------------|-----|
| Buy American Compliant | Yes |
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSB14FR](#)
- [Video - Heat Shrink Product Overview & Installation](#)