



# GD1526, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy  
Catalog # [GD1526](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG ( Sol.) - 2/0 AWG (Str.), 1-1/8" to 1-1/4" Rod, 1" Pipe.

## Application

For Joining A Range Of Two Parallel Cables To Rod Or Tube, Grounding Fence Posts, Direct Burial Applications In Earth Or Concrete

## General

EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GD
U Bolt Type	244
UPC	781810260258
UPC 12 Digit	7818102602588

## Dimensions

Dimension - B Length inch	1.13 in
Dimension - Height fraction	3-3/8 in
Dimension - Height inch	3.38 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

## Conductor Related

Conductor - Copper Solid Size Range	4;3;2;1;1/0;2/0
Conductor - Copper Str Size Range	4;3;2;1;1/0;2/0
Conductor - Copper Str Size Range	4 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	1-1/8;1-1/4
Conductor - Copper Tube Std Size Range	1-1/8-1-1/4
Conductor - Rod Size	1 1/4 in
Conductor - Rod Size Range	1 1/4 in

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [3D Models - GD1526\\_MODEL-STEP](#)
- [3D Models - GD1526\\_MODEL-IGES](#)
- [3D Models - GD1526\\_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR\\_gdla](#)
- [Sales Drawings - SD..013775-01](#)





A proud member of the Hubbell Family.