



HSB14FR, Heat Shrink Tubing, 0.250" ID Min.(Exp.), 0.125" ID Max. (Rec.), 12-10 Flex, PVC, Thin Wall, Flame Retardant, Black, 600V.



By Burndy
Catalog # [HSB14FR](#)

Heat Shrink Tubing, 0.250" ID Min.(Exp.), 0.125" ID Max.(Rec.), 12-10 Flex, PVC, Thin Wall, Flame Retardant, Black, 600V.

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

General

Catalog Number	HSB14FR
Connector Type	THIN WALL TUBES/REELS
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	HEAT SHRINK
Type	HS-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810265819

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12AWG -8AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSB14FR](#)
- [Video - Heat Shrink Product Overview & Installation](#)