



GD1629CG1TN, Mechanical Grounding Connector, 2 Cables to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GD1629CG1TN](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe; Accommodates: 1-1/4" IPS; 1-3/8" - 1-1/4" Rod; 2/0 Sol - 250 kcmil Copper Cable.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

Catalog Number	GD1629CG1TN
Installation Torque	360 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw	Steel - Galvanized
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin Plated
UPC	621945200807
UPC 14 Digit GTIN	00621945200807

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Height inch	4.12 in
Dimension - Height mm	104.6 mm
Dimension - Width fraction	3-1/4 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250

Conductor - Copper Str Size B Range	1.25
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - GD1629CG1TN_MODEL-PDF](#)
- [3D Models - GD1629CG1TN_MODEL-IGES](#)
- [3D Models - GD1629CG1TN_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - CSKC033484-01](#)
- [Specifications - GD1629CG1TN](#)