



GD1834, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD1834](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 300 - 500 kcmil, 2" Rod, 2" Pipe.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

Catalog Number	GD1834
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
U Bolt Type	260
UPC	781810260340
UPC 12 Digit	7818102603400

Dimensions

Dimension - B Length inch	1.56 in
Dimension - Height fraction	5-3/8 in
Dimension - Height inch	5.38 in
Dimension - Width fraction	4-1/8 in
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

Conductor Related

Conductor - Copper Str Size	300;350;400;450;500
Conductor - Copper Str Size B Range	2
Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Copper Tube Std Size	2
Conductor - Copper Tube Std Size Range	2
Conductor - Rod Size	2 in
Conductor - Rod Size Range	2 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [3D Models - GD1834_MODEL-IGES](#)
- [3D Models - GD1834_MODEL-PDF](#)
- [3D Models - GD1834_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_gdla](#)
- [Sales Drawings - SD..013775-01](#)
- [Specifications - GD1834](#)



A Hubbell brand