



HSB332T48PF, Thin Wall Cross-Linked Black Polyolefin Heat Shrink Tubing, #16-18 AWG, 600 V, Flame Retardant.



By Burndy
Catalog # [HSB332T48PF](#)

Thin Wall Cross-Linked Black Polyolefin Heat Shrink Tubing, #16-18 AWG, 600 V, Flame Retardant.

Application

For Terminations And Splices

General

Catalog Number	HSB332T48PF
Connector Type	THIN WALL REEL
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810212295

Conductor Related

Conductor Range	#18 AWG to #16 AWG
Conductor Size	18AWG - 16AWG

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSB332T48PF](#)