



GG192, Mech Ground, Cu Bar/Strap/Braid or Cable to Rod/Tube

By Burndy
Catalog # [GG192](#)

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 2-1/2" Pipe, 2-1/2"-2 7/8" Rod, 4.56 IN Width

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation
- Type GG connector is particularly effective for use with braid for ground rods, switch handles, fence posts and gates

Application

For Joining Copper Bar, Strap, Braid Or Cable To Rod Or Tube, Direct Burial Cables

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	No
Certification - CSA Approved	Yes

Dimensions

Package Height	0.000 in
Dimension - Height mm	127 mm



Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width mm	116 mm
Dimension - Width inch	4.56 in
Dimension - B Length inch	1.75 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Material Type - Screw Plated	DURIUM™ Silicon Bronze
Sub Brand	No
Product Type	MECHANICAL CONNECTOR
UPC	Mechanical
Type	781810990056
U Bolt Type	GG
Material	232
Plating Type	Copper Alloy, Cast
UPC 12 Digit	Unplated
UPC 14 Digit GTIN	781810990056
	00781810990056

Logistics

Minimum Pack Quantity	1
Pallet Quantity	54
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)