



HSIC200FREA, Heavy wall heat shrinkable end cap, 2.00" ID Min. (Exp.), 0.63" ID Max.(Rec.), 250 - 1111 kcmil (flex), Thick Wall, Black

By Burndy
Catalog # [HSIC200FREA](#)



Heavy wall heat shrinkable end cap, 2.00" ID Min.(Exp.), 0.63" ID Max.(Rec.), 250 - 1111 kcmil(flex), Polyolefin, Thick Wall, Black, Shrink ratio-3:1, 600V.

Features

- Heavy Wall Cross Linked Polyolefin
- UV94-VO
- Recognized Flame Retardant Material
- 3:1 Shrink Ratio
- Shrink Temperature of 150°C
- Blue Thermo-chromic lines disappear during correct installation
- Rated up to 600 Volts
- Sealing Adhesive
- Moisture and Water Resistant
- UL486D
- Insulates and Protects
- Direct Burial

General

Catalog Number	HSIC200FREA
Color	Black
Material	POLYOLEFIN
UPC	781810083178

Conductor Related

Conductor Range 250-1111 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	50
Minimum Pack Quantity	5

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSIC-FR_LineArt](#)
- [Sales Drawings - SC209680-01](#)
- [Specifications - HSIC200FREA](#)
- [Video - Heat Shrink Product Overview & Installation](#)