



HSIC350FR, Heavy wall heat shrinkable end cap, 3.50" ID Min. (Exp.), 1.18" ID Max.(Rec.), 1250 Kcmil AWG, Thick Wall, Black



By Burndy
Catalog # [HSIC350FR](#)

Heavy wall heat shrinkable end cap, 3.50" ID Min.(Exp.), 1.18" ID Max.(Rec.), 1250 Kcmil AWG, Polyolefin, Thick Wall, Black, Shrink ratio-3:1, 600V.

Features

- Heavy Wall Cross Linked Polyolefin
- UV94-VO
- Recognized Flame Retardant Material
- 3:1 Shrink Ratio
- Shrink Temperature of 150°C
- Blue Thermochromic lines disappear during correct installation
- Rated up to 600 Volts
- Sealing Adhesive
- Moisture and Water Resistant
- UL486D
- Insulates and Protects
- Direct Burial

General

Catalog Number	HSIC350FR
Color	Black
Connector Type	HEAVY WALL END CAP
Material	Cross-linked Polyolefin
UPC	781810266571

Conductor Related

Conductor Range	1250 Kcmil
Conductor Size	1250kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	7500
-----------------------	------

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Sales Drawings - SC209680-01](#)
- [Specifications - HSIC350FR](#)
- [Video - Heat Shrink Product Overview & Installation](#)