



HSR200FR, Heat Shrink Tubing, 2.00" ID Min.(Exp.), 1.00" ID Max. (Rec.), 500 - 750, PVC, Fire retardant, Thin Wall, Red, 25 Ft Reel.



By Burndy
Catalog # [HSR200FR](#)

Heat Shrink Tubing, 2.00" ID Min.(Exp.), 1.00" ID Max.(Rec.), 500 - 750, PVC, Fire retardant, Thin Wall, Red, 25 Ft Reel.

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

General

Catalog Number	HSR200FR
Color	Red
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266724

Conductor Related

Conductor Range	500-750 Kcmil
Conductor Size	800kcmil - 1000kcmil

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	8
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSR200FR](#)